

Environment cabinets

1.11 Environment cabinets



For safe and correct storage of non-flammable liquids and water polluting substances WGK 1-3 in small containers.

This product complies with the requirements of the German Equipment and Product Safety Law (GS mark).

The collection trays are made by a specialist firm in accordance with Art 19 I Wasserhaushaltsgesetz (WHG - Water Management Act).

- ▶ Sheet steel cabinet, RAL 7035 - light grey.
- ▶ Torsion resistant wing doors with box stiffeners, RAL 7035 - lichtgrau.
- ▶ Closed using turning handle with security lock, locks on 3 sides.
- ▶ Magnetic pocket for DIN A5 documents.
- ▶ Height-adjustable collection trays, galvanised optional material thickness 1 mm with general national technical approval Z-38.5-197 issued by DIBt Berlin or material thickness 3 mm with declaration of conformity (ÜHP) according to StawAR.
- ▶ Anti-tilt of the collection trays by locking device.
- ▶ 4 adjustable bases for alignment of floor unevenness for model L-1 and L-2.
- ▶ Ventilation through air vents in the rear panel of the cabinet for model L-1 und L-2.

Note

Not suitable for storage of flammable liquids.



① Environment cabinet **L 1** and ② environment cabinet **LS 1**



Air vents in the cabinet rear panel



Anti-tilt of the collection trays



Adjusting **bases** for to level out unevenness in the floor

Ordering information/Technical data/Dimensions

| Model | Width in mm | Depth in mm | Height in mm | No. collection trays | Material thickness collection trays in mm | Collection volume/ collection tray in l | Load bearing* / collection tray in kg | Ref. no. |
|---------------------------------|-------------|-------------|--------------|----------------------|---|---|---------------------------------------|----------------------|
| Environment cabinet LS 1 | 950 | 420 | 1016 | 2 | 1 (galvanised) | 16 | 50 | 20-101046-001 |
| Environment cabinet LS 2 | 950 | 420 | 1016 | 2 | 3 (galvanised) | 20 | 75 | 20-101046-003 |
| Environment cabinet L 1 | 950 | 420 | 1950 | 4 | 1 (galvanised) | 16 | 50 | 20-201046-001 |
| Environment cabinet L 2 | 950 | 420 | 1950 | 4 | 3 (galvanised) | 20 | 75 | 20-201046-003 |

Accessories

| | | | | | | | | |
|---|-----|-----|----|----------------|--|--|----|---------------------|
| - Additional collection tray for models LS 1, L 1 | 947 | 378 | 60 | 1 (galvanised) | | | 50 | 20-81046-124 |
| - Additional collection tray for models LS 2, L 2 | 947 | 378 | 60 | 3 (galvanised) | | | 75 | 20-81046-125 |

*Load bearing capacity with uniformly distributed load